



BALASTRO ELECTRÓNICO 2x32 W T8 120V-277V

Dimeable Encendido Rápido
Tipo de Control 0-10 Volts C.D. (4 hilos)

NI522, IZT2S32SC73M

Tipo de lámpara	No. de lámparas	Watt lámparas	Temp. de arranque (°F/°C)	Volts	Corriente de línea (A rcm)	Potencia de línea (W Watt)	THD (Máx.)	Factor de Potencia
F17T8	2	17	50/10	120-277	0.30/0.13 A	11/36	10	0.99
F25T8	2	25	50/10	120-277	0.43/0.19 A	12/52	10	0.99
F32T8	2	32	50/10	120-277	0.56/0.24 A	13/67	10	0.99



Longitud (L)	Ancho (W)	Alto (H)	Montaje (M)
24.10 cm	4.3 cm	3 cm	22.6 cm
9.50"	1.7"	1.18"	8.90"



Philips Lighting Electronics North America - Mexico
 Av. de la Palma, No. 6 Piso 2 Col. San Fernando, La Herradura, C.P. 52760, Huixquilucan, Edo. de México
 Tel: 5269-9316, Fax: 5269-9032
 La información técnica y comercial de nuestros productos puede ser modificada sin previo aviso.

