

		Id [mA]	# LEDs	Label Flux CW [lm]	Label Flux NW [lm]	Label Flux WW [lm]	P _{LED} [W]	P _{sys} [W]	PF	Drivercode
Bobek Class I	250		12	1350	1250	1000	9	12	0,83	B00
			20	2250	2100	1700	14	20	0,81	C00
			28	3150	2900	2350	20	27	0,86	C00
			40	4500	4150	3350	28	32	0,88	D00
	350		12	1850	1700	1350	12	15	0,89	B00
			20	3050	2850	2250	20	26	0,86	C00
			28	4300	3950	3150	28	35	0,9	C00
			40	6100	5650	4450	40	45	0,92	D00
	500		12	2500	2300	1850	18	21	0,92	B00
			20	4150	3850	3000	29	36	0,9	C00
			28	5800	5400	4150	41	49	0,93	C00
			40	8200	7600	5850	58	63	0,95	D00
	600		12	2950	2700	2100	22	25	0,94	B00
			20	4850	4500	3450	36	43	0,92	C00
			28	6700	6200	4750	50	58	0,95	C00
			40	9400	8700	6550	70	76	0,96	E00

		Id [mA]	# LEDs	Label Flux CW [lm]	Label Flux NW [lm]	Label Flux WW [lm]	P _{LED} [W]	P _{sys} [W]	PF	Drivercode
Bobek Class II	250		12	1350	1250	1000	9	12	0,83	B00
			20	2250	2100	1700	14	20	0,81	BB0
			28	3150	2900	2350	20	27	0,86	BB0
			40	4500	4150	3350	Not in Class II			
	350		12	1850	1700	1350	12	15	0,89	B00
			20	3050	2850	2250	20	26	0,86	BB0
			28	4300	3950	3150	28	35	0,9	BB0
			40	6100	5650	4450	Not in Class II			
	500		12	2500	2300	1850	18	21	0,92	B00
			20	4150	3850	3000	29	36	0,9	BB0
			28	5800	5400	4150	41	49	0,93	BB0
			40	8200	7600	5850	Not in Class II			
	600		12	2950	2700	2100	22	25	0,94	B00
			20	4850	4500	3450	36	43	0,92	BB0
			28	6700	6200	4750	50	58	0,95	BB0
			40	9400	8700	6550	Not in Class II			