



Energy efficient, long life  
LED security

Philips LED Motion Sensor



**PHILIPS**




## Safety and Security

The Philips LED motion sensor incorporates the latest in lighting technology with practical and user friendly features, including adjustable beam angles and sensor timer.

Designed as a total fit and forget solution, the EH313L LED motion and daylight sensor is the complete package with low energy usage and extra long life.


### Product Features

- 2 x 7.5w LED adjustable beam direction
- Bright 5000K colour temperature
- Up to 30,000 hours lifetime
- IP44 rated for outdoor use
- Powerful 1000 lumens light output



**Philips Lighting Australia**  
 A sector of Philips Electronics  
 Australia Limited  
 65 Epping Road,  
 North Ryde 2113  
 Australia  
 Tel: 1300 304 404  
[www.philips.com.au/lighting](http://www.philips.com.au/lighting)

**Philips Lighting**  
 Level 2, 1 Nugent Street, Grafton  
 Auckland 1023, New Zealand  
 Tel: + 64 9 355 4700 or  
 0800 454 448 (toll free - local only)  
 Fax: + 64 9 160 875 or  
 0800 160 875 (toll free - local only)  
[solutions.NZ@philips.com](mailto:solutions.NZ@philips.com)  
[www.philips.co.nz/lighting](http://www.philips.co.nz/lighting)



© 2013 Koninklijke Philips N.V.

All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent or other industrial or intellectual property rights.

Release date: May 2013