


American Metal Halide – Universal Operating – MHNasc

Sodium Scandium Metal Halide Lamps consisting of a gas filled glass bulb and an internal coated quartz discharge tube.



Product ID	C max.	D max.	L max.
250W	226	91	149
400W	290	121	184

Dimensions in mm

American Metal Halide – Universal Operating – MHNasc

Shortcode	Description	Wattage (W)	Cap Base	Voltage	Colour Rendering Index (Ra)	Luminous Flux (lm)	Average Lifetime (hrs)	Colour Temp (K)	Min Order Qty	Carton Qty
MH250	MH 250W /637 U E40 CO SLV/12	250	E40	133	61	19000	10000	3700	1	12
MH400	MH 400W /637 U E40 CO SLV/6	400	E40	135	61	33400	16000	3700	1	6