


Practitone Tubular

Small incandescent lamps for areas with limited space.



Product ID	Overall Length Diameter	
	C max.	D max.
15W B15 PILOT	52	22
15W B22 PILOT	52	25
15W E14 PILOT	57	25
15W E14 OVEN	49	22
25W E14 OVEN	57	25
25W E27 OVEN	61	29

Dimensions in mm

Pilot Oven Lamps

Shortcode	Wattage (W)	Cap Base	Voltage	Bulb Shape	Luminous Flux Lamp (lm)	Average Lifetime (hrs)	Colour Temperature (K)	Unit	Carton Qty
OVEN15T22	15	E14	230-240V	T22	90	1000	2700	PCE	10
OVEN25T25	25	E14	230-240V	T25	172	1000	2700	PCE	10
15BCPIL	15	B22	230-240V	T25	115	1000	2700	SET	5
15SESPIL	15	E14	230-240V	T25	115	1000	2700	PCE	10
15SBCT22CL	15	B15	220-240V	T22	172	1000	2700	PCE	5
15SEST25CL	15	E14	220-240V	T25	90	1000	2700	SET	5
40SEST25LCL	40	E14	240V	T25	424	1000	2700	PCE	10
25ESDECOT29	25	E27	230-240V	T29	162	1000	2700	PCE	5