


Brilliantline Pro Dichroic

A quality low voltage halogen reflector lamp consisting of a high pressure xenon gas filled burner, optically positioned in a Dichroic glass reflector. Designed to transmit heat through the back of the lamp and reflect light to the front, resulting in a “cool” beam. Brilliantline Pro lamps feature a high intensity beam with a clearly defined beam spread and have excellent lumen maintenance over their life. They come complete with front glass and the universal burning position. Lifetime 4,000 hours.



Product ID	Overall Length Diameter	
	C max.	D max.
GU5.3	46	50.8

Dimensions in mm

Brilliantline Pro Dichroic

Shortcode	Beam Angle	Wattage (W)	Cap Base	Voltage	Bulb Shape	Luminous Flux Lamp (lm)	Average Lifetime (hrs)	Colour Temperature (K)	Unit	Carton Quantity
BRIL122024	24°	20	GU5.3	12V	MR16	236	4000	3000	PCE	5
BRIL122036	36°	20	GU5.3	12V	MR16	236	4000	3000	PCE	5
BRIL122060	60°	20	GU5.3	12V	MR16	236	4000	3000	PCE	5
BRIL123536	36°	35	GU5.3	12V	MR16	500	4000	3000	PCE	5
BRIL123560	60°	35	GU5.3	12V	MR16	500	4000	3000	PCE	5
BRIL125036	36°	50	GU5.3	12V	MR16	775	4000	3000	PCE	5
BRIL125060	60°	50	GU5.3	12V	MR16	775	4000	3000	PCE	5