


CDO-ET Elliptical

The Mastercolour City range of high intensity discharge lamps feature a CDM Mastercolour discharge tube placed in a high pressure sodium lamp outer bulb. The result is a robust lamp which emits a pleasant light, with stable colour and excellent colour rendering (Ra>80), and which is compatible with a SON ballast and igniters.



CDO-ET

Product ID	C max.	D max.	O max.	L max.
CDO-ET 50W	156	71	N/A	N/A
CDO-ET 70W	156	71	N/A	N/A
CDO-ET 100W	186	76	N/A	N/A
CDO-ET 150W	227	91	N/A	N/A

Dimensions in mm

CDO-TT & CDO-ET Elliptical

Shortcode	Description	Wattage (W)	Cap Base	Luminous Intensity (cd)	Average Lifetime (hrs)	Colour Temp (K)	Min Order Qty	Carton Qty
CDOET50W828	MASTER CityWh CDO-ET Plus 50W/828 E27	50	E27	5150	20000	2800	24	24
CDOET70W828	MASTER CityWh CDO-ET Plus 70W/828 E27	70	E27	7230	27000	2900	24	24
CDOET100W828	MASTER CityWh CDO-ET Plus 100W/828 E40	100	E40	9400	27000	2890	12	12
CDOET150W828	MASTER CityWh CDO-ET Plus 150W/828 E40	150	E40	15100	27000	2830	12	12