


# CDO-TT

The Mastercolour City range of high intensity discharge lamps feature a CDM Mastercolour discharge tube placed in a high pressure sodium lamp outer bulb. The result is a robust lamp which emits a pleasant light, with stable colour and excellent colour rendering (Ra>80), and which is compatible with a SON ballast and igniters.



**CDO-TT**

Product ID	C max.	D max.	O max.	L max.
CDM-TT 70W	156	36	102	6
CDM-TT 150W	211	460	133	8
CDO-TT 70W	156	36	102	7.1
CDO-TT 100W	211	47	132	8.5
CDO-TT 150W	211	47	132	10
CDO-TT 250W	255	47	158	12.3

Dimensions in mm

## CDO-TT & CDO-ET Elliptical

Shortcode	Description	Wattage (W)	Cap Base	Luminous Intensity (cd)	Average Lifetime (hrs)	Colour Temp (K)	Min Order Qty	Carton Qty
CDMTT70W942	MASTERC CDM-TT 70W/942 E27 SLV/12	70	E27	6300	18000	4200	12	12
CDMTT150W942	MASTERC colour CDM-TT 150W/942 E40 1SL/12	150	E40	11200	20000	42000	12	12
CDOTT70W828	MASTER CityWh CDO-TT Plus 70W/828 E27	70	E27	7500	20000	2800	1	12
CDOTT100W828	MASTER CityWhite CDO-TT Plus 100W/828 E40	100	E40	10500	27000	2800	1	12
CDOTT150W828	MASTER CityWh CDO-TT Plus 150W/828 E40	150	E40	16500	27000	2800	1	12
CDOTT250W830	MASTER CityWhite CDO-TT Plus 250W/830 E40	250	E40	28300	23000	3000	12	12
CDOTT250W940	MASTER CityWhite CDO-TT Plus 250W/940 E40 1CT/12	250	E40	26500	18000	4000	1	12