


CosmoPolis Outdoor

New-generation ceramic metal-halide tubular lamps used in outdoor applications, offering efficient and pleasant white light. Attractive white-light alternative to current standard mercury-vapour, HPS and ceramic solutions. Designed for electronic gear platforms including all control features and dimming options offering flexible light levels and reduced energy consumption. Highly efficient white light; extremely high system efficacy.



Product ID	Overall Length C max	Diameter D max.	Arc Length O	Light Centre Length L
45W	132	20	15	59
60W	132	20	14	59
90W	143	20	18	66
140W	147	20	20	66

Dimensions in mm

CosmoPolis Outdoor

Shortcode	Description	Wattage (W)	Cap Base	Luminous Intensity (cd)	Average Lifetime (hrs)	Colour Temp (K)	Min Order Qty	Carton Qty
CPOTWHITE45W728	MST CosmoWh CPO-TW Xtra 45W/728 PGZ12	45	PGZ12	4950	32000	2815	12	12
CPOTWHITE60W728	MST CosmoWh CPO-TW Xtra 60W/728 PGZ12	60	PGZ12	7200	32000	2715	1	12
CPOTWHITE90W728	MST CosmoWh CPO-TW Xtra 90W/728 PGZ12	90	PGZ12	10800	32000	2870	1	12
CPOT140W728	MST CosmoWh CPO-TW Xtra 140W/728 PGZ12	140	PGZ12	17600	32000	2900	1	12
CPOTTX60WE27	MST CosmoWhite CPO-TT Xtra 60W/628 E27	60	E27	7090	32000	2800	12	12
CPOTTX90WE40	MST CosmoWhite CPO-TT Xtra 90W/628 E40	90	E40	10000	32000	2800	12	12
CPOTTX140WE40	MST CosmoWhite CPO-TT Xtra 140W/628 E40	140	E40	16800	32000	2800	12	12
CPOTTX210WE40	MST CosmoWhite CPO-TT Xtra 210W/942 E40	210	E40	22000	32000	4200	12	12
CPOTTX315WE40	MST CosmoWhite CPO-TT Xtra 315W/942 E40	315	E40	34750	30000	4200	12	12