


EcoClassic A55

New generation halogen-technology lamp to replace the standard GLS bulb. Offering the same shape, size, and dimming functions.



Product ID	C	D
A55	95.5	55

Dimensions in mm

EcoClassic A55 Clear

Shortcode	Wattage (W)	Cap Base	Voltage	Luminous Flux Lamp (lm)	Average Lifetime (hrs)	Colour Temperature (K)	Colour	Carton Quantity
ECO28WE27A55CL	28	E27	240	340	2000	2900	Clear	100
ECO28WB22A55CL	28	B22	240	340	2000	2900	Clear	100
ECO42WE27A55CL	42	E27	240	630	2000	2900	Clear	100
ECO42WB22A55CL	42	B22	240	630	2000	2900	Clear	100
ECO53WE27A55CL	53	E27	240	850	2000	2900	Clear	100
ECO53WB22A55CL	53	B22	240	850	2000	2900	Clear	100
ECO70WB22A55CL	70	B22	240	1200	2000	2900	Clear	100
ECO70WE27A55CL	70	E27	240	1200	2000	2900	Clear	100

EcoClassic A55 Frosted

Shortcode	Wattage (W)	Cap Base	Voltage	Luminous Flux Lamp (lm)	Average Lifetime (hrs)	Colour Temperature (K)	Colour	Carton Quantity
ECO28WE27A55FR	28	E27	240	340	2000	2900	Frosted	100
ECO28WB22A55FR	28	B22	240	340	2000	2900	Frosted	100
ECO42WE27A55FR	42	E27	240	630	2000	2900	Frosted	100
ECO42WB22A55FR	42	B22	240	630	2000	2900	Frosted	100
ECO53WE27A55FR	53	E27	240	850	2000	2900	Frosted	100
ECO53WB22A55FR	53	B22	240	850	2000	2900	Frosted	100
ECO70WB22A55FR	70	B22	240	1200	2000	2900	Frosted	100
ECO70WE27A55FR	70	E27	240	1200	2000	2900	Frosted	100
EC30A55105WBC	105	B22	240V	2100	2000	2900	Frosted	10
EC30A55140WBC	140	E27	240V	2800	2000	2900	Frosted	10