


# Ecotone High Lumen Twister

The Ecotone High Lumen lamps offer energy saving solutions in high lumen applications. Features an Air Pump system that blocks heat from the burner and provides forced cooling by pushing hot air out of the system. A recommended choice for direct replacement of ML blended mercury lamps.



Product ID	Overall Length C max.	Diameter D max.	Width F max.
45W	207	98	80.3
65W	223	98	80.3

Dimensions in mm

## Genie

Shortcode	Wattage (W)	Replaces	Cap Base	Voltage	Luminous Flux Lamp (lm)	Average Lifetime (hrs)	Colour Temp (K)	Carton Qty
EHLT45W840BC	45	100W ML	B22	220-240	3000	10000	4000	6
EHLT45W840ES	45	100W ML	E27	220-240	3000	10000	4000	6
EHLT65W840BC	65	160W ML	B22	220-240	4200	10000	4000	6
EHLT65W840ES	65	160W ML	E27	220-240	4200	10000	4000	6