


Essential Twistline Dichroic

A range of compact quartz halogen reflector lamps that offer a mains voltage look-alike to low voltage dichroic MR16 lamps. The lamp can be connected directly to 240V mains supply eliminating the need for a transformer. Featuring an aluminium reflector which directs most of the heat to the front to prevent overheating in the luminaire/ceiling space where ventilation is not adequate. Features a GU10 lamp base. Twistline provides a constant quality of light over lamp life and remains bright and shining.



Product ID	Overall Length C max.	Diameter D max.
GU10	51	51

Dimensions in mm

Essential Twistline Dichroic

Shortcode	Beam Angle	Wattage (W)	Cap Base	Voltage	Bulb Shape	Luminous Flux Lamp (lm)	Average Lifetime (hrs)	Colour Temperature (K)	Unit	Carton Quantity
ESS2403536	36°	35	GU10	240V	MR16	235	2000	3000	PCE	5
ESS2405036	36°	50	GU10	240V	MR16	385	2000	3000	PCE	5