


Essential Plus Dichroic

Low voltage halogen reflector lamps, designed to provide crisp white light. Feature a “cool” beam dichroic reflector and UV block on the burner. The closed version offers additional protection from UV via the glass front. Ideally suited for general purpose display and domestic lighting. Lifetime 3,000 hours.



Product ID	Overall Length Diameter	
	C max.	D max.
GU5.3	46	51

Dimensions in mm

Essential Plus Dichroic

Shortcode	Beam Angle	Wattage (W)	Cap Base	Voltage	Bulb Shape	Luminous Flux Lamp (lm)	Average Lifetime (hrs)	Colour Temperature (K)	Unit	Carton Quantity
HAL122036	36°	20	GU5.3	12V	MR16	230	2000	3000	PCE	10
HAL125036	36°	50	GU5.3	12V	MR16	750	2000	3000	PCE	10
HAL125060	60°	50	GU5.3	12V	MR16	750	2000	3000	PCE	10