


Floodlight PAR38

Made from hard pressed glass, making them suitable for indoor and outdoor applications. Spot versions have a stippled front reflector producing a narrow homogenous beam. Flood versions have a front refractor composed of prismatic elements.



Product ID	Overall Length Diameter	
	C max.	D max.
80W E27	137	122.5
120W E27	137	121
80W E27 Colour	137	122.5
80W E27 Anti Mosquito	137	121

Dimensions in mm

Floodlight PAR38

Shortcode	Wattage (W)	Cap Base	Voltage	Bulb Shape	Luminous Intensity (cd)	Average Lifetime (hrs)	Colour Temperature (K)	Unit	Carton Quantity
120PARFLOOD	120	E27	240V	PAR38	3100	2000	2700	PCE	6
80PARFLOOD	80	E27	240V	PAR38	1800	2000	2700	PCE	6