

# Starter Switches


Premium quality 2-pin flame-retardant polycarbonate ignitors for starting of fluorescent lamps on conventional electromagnetic circuits.

Controlled preheating of the lamp filaments and sufficient pulse voltage for longer lamp life.

Features a radio-interference suppression capacitor.

S2 starters for ignition in single-circuit operation 110-130V and series operation 220-240V.

S10 starters for ignition in series operation 220-240V.



Product ID	Overall Length C max.	Diameter E max.
S2	40.3	21.5
S10	40.3	21.5
S16	40.6	21.5

Dimensions in mm

## Starter Switches

Shortcode	Wattage	Min Order Quantity	Carton Quantity
S2	4-22	25	300
S10	4-65	25	300
S16	70-125	10	200