


# HPI PLUS Quartz Metal Halide

Energy saving compact fluorescent lamp. Compact long-arc low-pressure mercury discharge lamp envelope consists of 6 parallel narrow fluorescent tubes.

- Features:**
- Ovoid, internally white coated outer bulb.
  - 3-band technology resulting in high luminous efficacy, both initially and over long lifetime.
  - Available in cool white and daylight colour appearance demonstrating good colour stability.
  - “S”- type for direct retrofit for HPL lamps.
  - “P”- type for use without protective front shield.

- Luminaires:**
- HPI Plus BU-P and BUS-P suitable for use in open luminaires.
  - For other HPI Plus lamps a protective front glass is required.

- System:**
- Can be run on HPI-gear as well as on SON-gear (“Plus”-concept). The results in both light output and colour temperature are different.
  - HPI Plus BUS and BUS-P types require an HPL-gear and no ignitor.



Product ID	Overall Length C max.	Diameter D max.
250W	226	91
400W	290	122

Dimensions in mm

## MASTER HPI Plus Quartz Coated Metal Halide Lamp – Ovoid Coated (Base up, Ignitor required)

Shortcode	Description	Wattage (W)	Cap Base	Voltage	Colour Rendering Index (Ra)	Luminous Flux (lm)	Average Lifetime (hrs)	Colour Temp (K)	Min Order Qty	Carton Qty
HPI250WBU	HPI PLUS 250W /745 BU E40 SLV/12	250	E40	128	65	18000	20000	4500	1	12
HPI400WBU	HPI PLUS 400W /745 BU E40 SLV/6	400	E40	125	65	32500	20000	4500	1	6

## MASTER HPI Plus Quartz Metal Halide Lamp – Daylight Ovoid Coated (Base up, Ignitor required)

Shortcode	Description	Wattage (W)	Cap Base	Voltage	Colour Rendering Index (Ra)	Luminous Flux (lm)	Average Lifetime (hrs)	Colour Temp (K)	Min Order Qty	Carton Qty
HPI250W667BU	HPI PLUS 250W/667BU E40 1SL/12	250	E40	128	69	18000	20000	6700	12	12
HPI400W667BU	HPI PLUS 400W/667 BU E40 1SL/6	400	E40	125	69	32500	20000	6700	6	6

# HPI PLUS Quartz Metal Halide continued

MASTER HPI Plus Ovoid Coated, (Base up, Ignitor required, Protected)										
Shortcode	Description	Wattage (W)	Cap Base	Luminous Flux (lm)	Average Lifetime (hrs)	Colour Temp (K)	Min Order Qty	Carton Qty	Trade Price	
HP1250WBUP	MASTER HPI Plus 250W/645 BU-P E40 SLV/12	250	E40	18000	20000	4500	12	12	\$230.00	
HP1400WBUP	MASTER HPI Plus 400W/645 BU-P E40 SLV/6	400	E40	32500	20000	4500	1	6	\$230.00	

MASTER HPI Plus Ovoid Coated (Base up, Self Start, no ignitor required)										
Shortcode	Description	Wattage (W)	Cap Base	Luminous Flux (lm)	Average Lifetime (hrs)	Colour Temp (K)	Min Order Qty	Carton Qty	Trade Price	
HP1400WBUS	HPI-PLUS 400W BUS645 E40.15LV/6	400	E40	32500	20000	4500	1	6	\$228.00	

MASTER HPI Plus Ovoid Coated, (Self Start, no ignitor required, Protected )										
Shortcode	Description	Wattage (W)	Cap Base	Luminous Flux (lm)	Average Lifetime (hrs)	Colour Temp (K)	Min Order Qty	Carton Qty	Trade Price	
HP1400WBUSP	MASTER HPI Plus 400W/645 BUS-P E40 SLV/6	400	E40	32500	20000	4500	6	6	\$255.00	