


MASTER CDM-R Mini

Provides users with a compact, high-efficiency, discharge reflector lamp. Low operating costs, long-lamp life, UV block for reduced fading risk and a stable colour impression all benefit the shop owner. Low heat output and crisp, sparkling light, enhances the experience for shoppers and staff. Requires CDM electronic HID driver.



Product ID	A max.	C max.	C1 max.	D max.
20W	59	65.4	60.9	51

Dimensions in mm

MASTER CDM-R Mini

Shortcode	Description	Wattage (W)	Cap Base	Voltage	Colour Rendering Index (Ra)	Luminous Flux (lm)	Average Lifetime (hrs)	Colour Temp (K)	Min Order Qty	Carton Qty
CDMRM20W83025	CDM-Rm Mini 20W/830 GX10 MR16 25D	20	GX10	93	84	4500	15000	3000	12	12
CDMRM20W83040	CDM-Rm Mini 20W/830 GX10 MR16 40D	20	GX10	93	84	2100	15000	3000	12	12