


MASTER CDM-R PAR 20 Elite

Provides users with a compact, high-efficiency, discharge reflector lamp. Low operating costs, long-lamp life, UV block for reduced fading risk and a stable colour impression all benefit the shop owner. Low heat output and crisp, sparkling light, enhances the experience for shoppers and staff.



Product ID	Overall Length C max.	Diameter D max.
PAR20	95	65

Dimensions in mm

MASTER CDM-R PAR 20

Shortcode	Description	Wattage (W)	Cap Base	Voltage	Colour Rendering Index (Ra)	Luminous Flux (lm)	Average Lifetime (hrs)	Colour Temp (K)	Min Order Qty	Carton Qty
CDMRE35W9302010	MC CDM-R Elite 35W/930 E27 PAR20 10D	35	E27	88	91	23000	15000	3000	12	12
CDMRE35W9302030	MC CDM-R Elite 35W/930 E27 PAR20 30D	35	E27	88	91	6500	15000	3000	12	12