


# MASTER CDM-R PAR 30

Compact, high-efficiency, long-life Ceramic Metal Halide discharge reflector lamp producing crisp white sparkling light with good colour rendering that enhances the look of merchandise. Stable colour over lifetime. Easy to install in simple open luminaires, reducing installation and relamping costs.



Product ID	Overall Length C max.	Diameter D max.
PAR30L	123	95

Dimensions in mm

## MASTER CDM-R PAR 30

Shortcode	Description	Wattage (W)	Cap Base	Luminous Intensity (cd)	Average Lifetime (hrs)	Colour Temp (K)	Min Order Qty	Carton Qty
CDMR70W9423010	CDM-R 70W /942 E27 PAR30L 10D 1CT/6	70	E27	63000	12000	4200	1	12
CDMR70W9423030	CDM-R 70W /942 E27 PAR30L 30D 1CT/6	70	E27	13000	12000	4200	1	12
CDMR70W9423040	CDM-R 70W /942 E27 PAR30L 40D 1CT/6	70	E27	9000	12000	4200	1	12