


MASTER CDM-R PAR 30 Elite

Compact, very high-efficiency, long-life Ceramic Metal Halide discharge reflector lamp producing crisp white sparkling light with high colour rendering that makes merchandise look irresistible. Stable colour and lumen output over life keeps your store attractive season after season. Easy to install in simple open luminaires, reducing installation and relamping costs.

MASTER CDM-R PAR 30 Elite

Shortcode	Description	Wattage (W)	Cap Base	Voltage	Colour Rendering Index (Ra)	Luminous Flux (lm)	Average Lifetime (hrs)	Colour Temp (K)	Min Order Qty	Carton Qty
CDMRE35W9303010	MC CDM-R Elite 35W/930 E27 PAR30L 10D	35	E27	92	91	49000	15000	3000	6	6
CDMRE35W9303030	MC CDM-R Elite 35W/930 E27 PAR30L 30D	35	E27	92	91	8000	15000	3000	6	6
CDMRE50W9303010	MC CDM-R Elite 50W/930 E27 PAR30L 10D	50	E27	94	91	56000	15000	3000	6	6
CDMRE50W9303030	MC CDM-R Elite 50W/930 E27 PAR30L 30D	50	E27	94	91	11000	15000	3000	12	12
CDMRE50W9303040	MC CDM-R Elite 50W/930 E27 PAR30L 40D	50	E27	94	91	7200	15000	3000	12	12
CDMRE70W9303010	MC CDM-R Elite 70W/930 E27 PAR30L 10D	70	E27	86	92	61000	15000	3000	6	6
CDMRE70W9303030	MC CDM-R Elite 70W/930 E27 PAR30L 30D	70	E27	86	92	14000	15000	3000	6	6
CDMRE70W9303040	MC CDM-R Elite 70W/930 E27 PAR30L 40D	70	E27	86	92	10300	15000	3000	1	6



Product ID	Overall Length C max.	Diameter D max.
PAR30L	123	95

Dimensions in mm