


# MASTER CDM-T

Range of single-ended, compact, high-efficiency, discharge lamps with a stable colour over lifetime and a crisp, sparkling light. Long lamp life compared with incandescent and halogen lamps. Low heat output and UV-block for reduced fading risks. Available in small CDM-T, for use with ballast and ignitor or electronic gear.



Product ID	C max.	D max.	L max.	O
150W	110	20	57	8
250W	135	25	73	12.3

Dimensions in mm

## MASTER CDM-T

Shortcode	Description	Wattage (W)	Cap Base	Voltage	Colour Rendering Index (Ra)	Luminous Flux (lm)	Average Lifetime (hrs)	Colour Temp (K)	Min Order Qty	Carton Qty
CDMT150W942	MASTERC CDM-T 150W/942 G12 ICT/12	150	G12	90	96	12700	12000	4200	12	12
CDMT250W830	MASTERC CDM-T 250W/830 G12 ICT/12	250	G12	95	85	27540	12000	3000	12	12
CDMT250W942	MASTERC CDM-T 250W/942 G12 ICT/12	250	G12	93	91	26000	12000	4200	10	10