


MASTER CDM-TC Elite

Single-ended, very high-efficiency, long-life Ceramic Metal Halide discharge lamp producing crisp white sparkling light with high colour rendering. High-intensity beam of crisp white sparkling light makes merchandise look irresistible. Stable colour and lumen output over life keeps your store attractive season after season. Lower Total Cost of Ownership as a result of high efficacy (same light, less energy or same energy, more light) and long life.



Product ID	C max.	D max.	L max.	O
35W	85	15	53	4.8
50W	85	15	53	7.1
70W	58	15	53	7.1

Dimensions in mm

MASTER CDM-TC Elite

Shortcode	Description	Wattage (W)	Cap Base	Voltage	Colour Rendering Index (Ra)	Luminous Flux (lm)	Average Lifetime (hrs)	Colour Temp (K)	Min Order Qty	Carton Qty
CDMTC35W930	MASTERC CDM-TC Elite 35W/930 G8.5 ICT/12	35	G8.5	85	90	4000	15000	3000	1	12
CDMTC35W942	MASTERC CDM-TC Elite 35W/942 G8.5 ICT	35	G8.5	84	88	3700	15000	4200	1	12
CDMTC50W930	MASTERC CDM-TC Elite 50W/930 G8.5 ICT/12	50	G8.5	93	90	5400	15000	3000	12	12
CDMTC50W942	MASTERC CDM-TC Elite 50W/942 G8.5 ICT	50	G8.5	90	90	5100	15000	4200	12	12
CDMTC70W930	MASTERC CDM-TC Elite 70W/930 G8.5 ICT/12	70	G8.5	85	90	7700	15000	3000	1	12
CDMTC70W942	MASTERC CDM-TC Elite 70W/942 G8.5 ICT	70	G8.5	84	90	7400	15000	4200	1	12