


MASTER CDM-TC Evolution

Single-ended, highest-efficiency, longest-life Ceramic Metal Halide discharge lamp producing crisp white sparkling light with high colour rendering. High-intensity beam of crisp white sparkling light makes merchandise look irresistible. Stable colour and lumen output over life keeps your store attractive season after season. Lowest Total Cost of Ownership as a result of high efficacy (same light, less energy or same energy, more light) and long life. Use only with electronic control gear.



Product ID	C max.	D max.	L max.	O
20W	85.0	15.0	53.0	3.6
35W	85.0	15.0	53.0	5.5
50W	85.0	15.0	53.0	7.2
70W	85.0	15.0	53.0	9.0

Dimensions in mm

MASTER CDM-TC Evolution

Shortcode	Description	Wattage (W)	Cap Base	Voltage	Colour Rendering Index (Ra)	Luminous Flux (lm)	Average Lifetime (hrs)	Colour Temp (K)	Min Order Qty	Carton Qty
CDMTCEVO20W930	MASTERC colour CDM-TC Evolution 20W/930 G8.5	20	G8.5	105	90	2050	20000	3000	12	12
CDMTCEVO35W930	MASTERC colour CDM-TC Evolution 35W/930 G8.5	35	G8.5	102	90	4300	20000	3000	12	12
CDMTCEVO50W930	MASTERC CDM-TC Evolution 50W/930 G8.5	50	G8.5	97	90	5700	20000	3000	12	12
CDMTCEVO70W930	MASTERC CDM-TC Evolution 70W/930 G8.5	70	G8.5	97	90	8800	20000	3000	12	12