


MASTER CDM-TD

CDM-TD range of double-ended, compact, high-efficiency, discharge lamps with a stable colour over lifetime and a crisp, sparkling light. UV-block for reduced health and fading risks. Direct retrofit in place for quartz metal halide lamps providing lower operating costs, reduced heat output, and better light quality.



Product ID	C max.	D max.	O
CDMTD70W830	120	22	8
CDMTD70W942	120	22	7
CDMTD150W830	137	25	10
CDMTD150W942	137	25	10

Dimensions in mm

Master CDM-TD

Shortcode	Description	Wattage (W)	Cap Base	Luminous Flux (lm)	Average Lifetime (hrs)	Colour Temp (K)	Min Order Qty	Carton Qty
CDMTD70W830	MASTERC CDM-TD 70W/830 RX7s 1CT/12	70	RX7s	6500	15000	3000	1	12
CDMTD70W942	MASTERC CDM-TD 70W/942 RX7s 1CT/12	70	RX7s	6000	15000	4200	1	12
CDMTD150W830	MASTERC CDM-TD 150W/830 RX7s 1CT/12	150	RX7s	13250	15000	3000	1	12
CDMTD150W942	MASTERC CDM-TD 150W/942 RX7s 1CT/12	150	RX7s	14200	15000	4200	1	12