


MASTER CDM-T Elite

Single-ended, very high-efficiency, long-life Ceramic Metal Halide discharge lamp producing crisp white sparkling light with high colour rendering. High-intensity beam of crisp white sparkling light makes merchandise look irresistible. Stable colour and lumen output over life keeps your store attractive season after season. Lower Total Cost of Ownership as a result of high efficacy (same light, less energy or same energy, more light) and long life.



Product ID	C max.	D max.	L max.	O
35W	103	20	57	4.8
50W	103	20	57	7.1
70W	103	20	57	7.15
100W	110	20	57	8.5
150W	135	24	73.5	10

Dimensions in mm

MASTER CDM-T Elite

Shortcode	Description	Wattage (W)	Cap Base	Volatge	Colour Rendering Index (Ra)	Luminous Flux (lm)	Average Lifetime (hrs)	Colour Temp (K)	Min Order Qty	Carton Qty
CDMT35W930	MASTERC CDM-T Elite 35W/930 G12 1CT/12	35	G12	85	90	4000	15000	3000	1	12
CDMT35W942	MASTERC CDM-T Elite 35W/942 G12 1CT	35	G12	84	90	3800	15000	4200	1	12
CDMT50W930	MASTERC CDM-T Elite 50W/930 G12 1CT/12	50	G12	90	90	5400	15000	3000	12	12
CDMT50W942	MASTERC CDM-T Elite 50W/942 G12 1CT	50	G12	91	90	5000	15000	4200	12	12
CDMT70W930	MASTERC CDM-T Elite 70W/930 G12 1CT/12	70	G12	85	90	7800	15000	3000	1	12
CDMT70W942	MASTERC CDM-T Elite 70W/942 G12 1CT/12	70	G12	84	90	7500	15000	4000	1	12
CDMT100W930	MASTERC CDM-T Elite 100W/930 G12 1CT/12	100	G12	88	92	11000	15000	3000	1	12
CDMT100W942	MASTERC CDM-T Elite 100W/942 G12 1CT	100	G12	88	91	10500	15000	4200	1	12
CDMT150W930	MASTERC CDM-T Elite 150W/930 G12 1CT/12	150	G12	92	92	15000	15000	3000	1	12