


MASTER CDM-T Elite Medium Wattage

The medium wattage lighting system that gives superior, longer-lasting white light for both indoor and outdoor use. Long reliable lifetime combined with high system efficacy. Outdoor Applications; floodlighting of buildings and other interesting structures. Illumination of roads and pedestrian areas, public spaces, car parks, petrol stations etc. Indoor Applications; larger (high-bay) retail outlets, warehouses, manufacturing facilities etc.



Product ID	C max.	D max.
CDMTMW210W930	188	29
CDMTMW210W942	193	38
CDMTMW315W930	188	29
CDMTMW315W942	193	38

Dimensions in mm

MASTER CDM-T Elite Medium Wattage

Shortcode	Description	Wattage (W)	Cap Base	Voltage	Colour Rendering Index (Ra)	Luminous Flux (lm)	Average Lifetime (hrs)	Colour Temp (K)	Min Order Qty	Carton Qty
CDMTMW210W930	CDM-T Elite 210W/930 PGZ18.1CT/12	210W	PGZ18	100	90	24150	30000	2940	12	12
CDMTMW210W942	CDM T12 ELITE 210W/942/U/O EU	210W	PGZX18.	105	92	22800	30000	3960	12	12
CDMTMW315W930	CDM-T Elite 315W/930 PGZ18.1CT/12	315W	PGZ18	100	90	38700	30000	3090	12	12
CDMTMW315W942	CDM Elite TMW 315/942/U/O EU	315W	PGZX18.	100	90	34300	30000	4140	12	12