


MASTER CDM-T Evolution

Single-ended, highest-efficiency, longest-life Ceramic Metal Halide discharge lamp producing crisp white sparkling light with high colour rendering. High-intensity beam of crisp white sparkling light makes merchandise look irresistible. Stable colour and lumen output over life keeps your store attractive season after season. Lowest Total Cost of Ownership as a result of high efficacy (same light, less energy or same energy, more light) and long life. Use only with electronic control gear.



Product ID	C max.	D max.	L max.	O
20W	103.0	20.0	57	3.6
35W	103.0	20.0	57	5.5
50W	103.0	20.0	57	7.2
70W	103.0	20.0	57	9.0

Dimensions in mm

MASTER CDM-T Evolution

Shortcode	Description	Wattage (W)	Cap Base	Voltage	Colour Rendering Index (Ra)	Luminous Flux (lm)	Average Lifetime (hrs)	Colour Temp (K)	Min Order Qty	Carton Qty
CDMTEVO20W930	MASTERC colour CDM-T Evolution 20W/930 G12	20	G12	105	90	2050	20000	3000	12	12
CDMTEVO35W930	MASTERC colour CDM-T Evolution 35W/930 G12	35	G12	102	90	4300	20000	3000	12	12
CDMTEVO50W930	MASTERC CDM-T Evolution 50W/930 OEM G12	50	G12	95	90	5700	20000	3000	12	12
CDMTEVO70W930	MASTERC CDM-T Evolution 70W/930 OEM G12	70	G12	96	90	8800	20000	3000	12	12