




MASTER LEDbulb A60

The new MASTER LED A60 10W bulb delivers a dimmable glow effect similar to a 60W incandescent bulb for a welcoming, warm atmosphere, making it ideal for general lighting applications. Its innovative design radiates warm light in all directions, making it a good alternative to the incandescent lamp.



Product ID	C max.	D max.
10W	122.6	66.0

Dimensions in mm

* Image guide only.

LEDbulb A60

Shortcode	Wattage (W)	Cap Base	Voltage	Lumen Output (lm)	Average Lifetime (hrs)	Colour Temp (K)	Min Order Quantity	Carton Qty
MAS10WDE27A67WW	10	E27	220-240	806	25000	2700	6	6
MAS10WDB22A67WW	10	B22	220-240	806	25000	2700	6	6

Dimming compatibility for Master LED A60 10W

Brand	Type #	Load	Operation Condition	Max no. of lamps
Clipsal	31E800T	Trailing	800W	1-8
Clipsal	32E2CFLDM	Trailing	300W	1-5
Clipsal	32E450LM	Leading	450W	1-8
Clipsal	32E450TM	Trailing	450W	1-8
Clipsal	32E450UDM	Universal	450W	1-8
Clipsal	E3031HD	Universal	40-60W	1
KIWI	K400U	Universal	400W	1-7
KIWI	K005T	Trailing	500W	1-8
PDL	654MWH	Trailing	20-450W	1-8
PDL	624TMWH	Universal	20-450W	1-8