




MASTER LEDspot AR111 Dimmable

Delivering a warm, halogen-like accent beam, MASTER LEDspot LV AR111 is an ideal retrofit solution for spot and general lighting applications in the hospitality and retail industry. It is particularly suitable for general lighting and creative accent lighting applications in shops, restaurants, hotels, and museums. Direct retrofit to existing halogen transformers.



| Product ID | Overall Length Diameter | |
|------------|-------------------------|--------|
| | C max. | D max. |
| 15W | 56 | 111 |

Dimensions in mm

MASTER LEDspot AR111 - Non Dimmable

| Shortcode | Wattage (W) | Cap Base | Voltage (V) | Luminous Intensity (cd) | Lumen Output (lm) | Average Lifetime (hrs) | Colour Temp (K) | Beam Angle ° | Min Order Qty | Carton Qty |
|-----------------|-------------|----------|-------------|-------------------------|-------------------|------------------------|-----------------|--------------|---------------|------------|
| 15WDAR11183024D | 15 | G53 | 12 | 4950 | 840 | 40000 | 3000 | 24 | 6 | 6 |
| 15WDAR11183040D | 15 | G53 | 12 | 1700 | 800 | 40000 | 3000 | 40 | 1 | 6 |

7 W MR16 7.2 W MR16

| Brand | Model | Type | Load | Lamps | philips et-s60 | osram htm70 | osram redback 60va | tridonic speedy | tridonic possum | tridonic viper |
|---------|-----------|-----------|------|-------|----------------|-------------|--------------------|-----------------|-----------------|----------------|
| Clipsal | 32E450UDM | Universal | 450W | '1-6 | ■ | | | | | |
| Clipsal | 32E450TM | Trailing | 450W | '1-6 | ■ | | | | | |
| Clipsal | 32E450LM | Leading | 450W | '1-6 | | | | | | |
| HPM | Cat 400L | Leading | 400W | '1-5 | | ■ | | | | |
| HPM | Cat 400T | Trailing | 400W | '1-5 | | ■ | | | | |
| PDL | 624TMWH | Trailing | 450W | '1-6 | | ■ | | | | |
| KIWI | K004U | Universal | 400W | '1-5 | | | | | | |
| KIWI | K005T | Trailing | 500W | '1-6 | | | | | | |