



MASTER LEDspot Low Voltage MR16 – Non-dimmable

Delivering a warm, halogen/incandescent-like accent beam, MASTER LEDspot MR16 non-dimmable lamp is an ideal retrofit solution for spot and general lighting applications where dimming is not required. It is particularly suited to public areas such as receptions, lobbies, corridors, stairwells and washrooms in the hospitality industry. These lamps provide an alternative to traditional GU5.3 halogen reflector lamps.



Product ID	Overall Length Diameter	
	C max.	D max.
4W	47.8	50
5.5W	47.8	50

Dimensions in mm

*image guide only.

LEDspot Low Voltage MR16 – Non-dimmable

Shortcode	Wattage (W)	Cap Base	Voltage (V)	Luminous Intensity (cd)	Luminous Flux (lm)	Average Lifetime (hrs)	Colour Temp (K)	Beam Angle °	Min Order Quantity	Carton Qty
MAS4WMR16WW24D	4	GU5.3	12	1100	210	25000	2700	24	1	10
MAS4WMR16WH24D	4	GU5.3	12	1150	220	25000	3000	24	1	10
5.5WMR16WW36D	5.5	GU5.3	12	800	415	25000	2700	36	1	10
5.5WMR16WH36D	5.5	GU5.3	12	820	425	25000	3000	36	1	10