




## MASTER LEDspot PAR

With its robust design and warm-white beam of light, PAR lamps are ideal for general lighting and spot lighting in the hospitality industry. They are especially suitable for public areas such as lobbies, corridors, and stairwells. Compatible with existing fixtures with an E27 holder and designed for retrofit replacement of halogen lamps.



\*Image guide only.

Product ID	Overall Length Diameter	
	C max.	D max.
9.5W	94.1	92

Dimensions in mm

### LEDspot PAR

Shortcode	Wattage (W)	Cap Base	Voltage	Lumen Output (lm)	Average Lifetime (hrs)	Colour Temp (K)	Beam Angle °	Min Order Qty	Carton Qty	Dimmable
MAS9.5WPAR30DIM	9.5	E27	220-240V	650	40000	2700	25	6	6	Yes

### 14.5 W PAR38

Brand	Model	Type	Load	Lamps
Clipsal	31E800T	Trailing	800W	1-8
Clipsal	32E2CFLDM	Trailing	300W	1-4
Clipsal	32E45OLM	Leading	450W	1-5
Clipsal	32E450TM	Trailing	450W	1-5
Clipsal	32E450UDM	Universal	450W	1-5
KIWI	K400U	Universal	400W	1-4
KIWI	KO05T	Trailing	500W	1-5
PDL	654MWH	Trailing	20-450W	1-5
PDL	624TMWH	Universal	20-450W	1-5