


# MASTER PL-L 4-PIN

PL-L lamps have two parallel fluorescent tubes and a 4-pin base. Dimming possible on electronic gear.



Product ID	A max.	B max.	C max.	D max.	D1 max.
18W	194.2	220.0	226.6	39	18
24W	289.2	315.0	321.6	39	18
36W	384.2	410.0	416.6	39	18
40W	509.2	535.0	541.6	39	18
55W	539.2	565.0	571.6	39	18

Dimensions in mm

## MASTER PL-L 4-PIN

Shortcode	Wattage (W)	Cap Base	Luminous Flux Lamp (lm)	Average Lifetime (hrs)	Colour Rendering Index (Ra)	Colour Temp (K)	Min Order Quantity	Carton Qty
PLL18W8404P	18	2G11	1200	20000	82	4000	1	25
PLL24W8404P	24	2G11	1800	20000	82	4000	1	25
PLL36W8404P	36	2G11	2900	20000	82	4000	1	25
PLL40W8404P	40	2G11	3500	20000	82	4000	1	25
PLL55W8404P	55	2G11	4800	20000	82	4000	1	25