


# MASTER PL-R Eco

MASTER PL-R-Eco is an extremely efficient compact fluorescent lamp for downlight applications. It consists of six parallel tubes with a new innovative ‘Twist and Lock’ lamp base, designed for use with electronic gear.

- Benefits:
- Optimal light and efficiency performance for short or long operation per switch in indoor downlighters
  - Up to 50% less energy consumption in application versus 18 and 26 W PL-C/T on EM gears for comparable lighting levels
  - Up to 25% less energy consumption in application versus 18 and 26 W PL-C/T on HF drivers for comparable lighting levels
  - Long life, sustainable light output and less early failures lead to less hassle and lower maintenance costs and facilitate the change from spot to group replacement
  - Easy lamp (re-)placement and stable fixation due to new twist and lock lampbase/holder



MASTER PL-R Eco								
Shortcode	Wattage (W)	Cap Base	Luminous Flux Lamp (lm)	Average Lifetime (hrs)	Colour Rendering Index (Ra)	Colour Temperature (K)	Min Order Quantity	Carton Quantity
PLR14W830	14	GR14q-1	1200	24000	82	3000	10	10
PLR14W840	14	GR14q-1	1200	24000	82	4000	10	10
PLR17W830	17	GR14q-1	1500	24000	82	3000	10	10
PLR17W840	17	GR14q-1	1500	24000	82	4000	10	10