


# MASTER PL-S 4-PIN

PL-S lamps are compact, single ended fluorescent lamps, with two parallel tubes. They have either a 2-pin or 4-pin base incorporating a special instant starter and capacitor.



Product ID	A max.	B max.	C max.	D max.	D1 max.
7W	96.0	113.0	119.1	28	13
9W	128.0	145.0	151.1	28	13
11W	196.0	214.0	219.9	28	13

Dimensions in mm

## PL-S 4-PIN

Shortcode	Wattage (W)	Cap Base	Luminous Flux Lamp (lm)	Average Lifetime (hrs)	Colour Rendering Index (Ra)	Colour Temp (K)	Min Order Quantity	Carton Qty
PLS7W8404P	7	2G7	400	13000	82	4000	50	50
PLS9W8404P	9	2G7	600	13000	82	4000	1	50
PLS11W8274P	11	2G7	900	13000	82	2700	50	50
PLS11W8404P	11	2G7	900	13000	82	4000	1	50