


MASTER PL-T 2-PIN

PL-T lamps are compact, single ended fluorescent lamps. All require external control gear which normally comes complete with the luminaire.



Product ID	A max.	B max.	C max.	D max.
18W	71.8	96	119.2	41.0
26W	86.7	111.0	134.2	41.0

Dimensions in mm

PL-T 2-PIN

Shortcode	Wattage (W)	Cap Base	Luminous Flux Lamp (lm)	Average Lifetime (hrs)	Colour Temp (K)	Min Order Quantity	Carton Qty
PLT18W8302P	18	Gx24d-2	1200	10000	3000	50	50
PLT26W8302P	26	Gx24d-3	1800	10000	3000	50	50
PLT26W8402P	26	Gx24d-3	1800	10000	4000	1	50