


MASTER PL-T 4-PIN

MASTER PL-T is an efficient compact fluorescent lamp, typically used in general downlights for retail, hospitality and office applications demanding higher lighting levels. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 4-pin version is designed for operation on electronic gear and is provided with a plug-in/pull-out lamp base.



Product ID	A max.	B max.	C max.	D max.
32W	98.7	123.0	138.7	41
42W	120.7	145.0	160.7	41

Dimensions in mm

MASTER PL-T 4-PIN

Shortcode	Wattage (W)	Cap Base	Luminous Flux (250, lm)	Average Lifetime (hrs)	Colour Rendering Index (Ra)	Colour Temp (K)	Min Order Quantity	Carton Qty
PLT32W8304P	32	GX24q-3	2400	13000	82	3000	50	50
PLT32W8404P	32	GX24q-3	2400	13000	82	4000	50	50
PLT42W8304P	42	GX24q-3	3200	13000	82	3000	50	50
PLT42W8404P	42	GX24q-3	3200	13000	82	4000	1	50