


MASTER TL5 Circular

16mm tube diameter circular fluorescent lamps with a choice of various diameters.

- Benefits:**
- Slim 16mm tube allows creation of extremely flat luminaires
 - Allows appealing circular designs
 - High lamp efficacy
 - Good colour rendering
 - Temperature independent light output
 - Higher average system efficiency

- Features:**
- Perfect circular shape
 - Highly efficient 3-band fluorescent coating
 - Specifically designed for operation with electronic gear
 - Can be ignited from -15 to +50°C
 - Amalgam technology

- Application:**
- Brings the benefits of TL5 lighting to an even wider range of attractive applications
 - Suitable for a wide range of professional and semi-professional applications
 - Ideal for use in shops, offices and public areas with non-traditional layouts
 - Amalgam lamps have limited suitability for dimming applications.



Product ID	D max.	E max.	I max.
22W	18	230	197
40W/55W	18	305	272
60W	18	379	346

Dimensions in mm

MASTER TL5 Circular

Shortcode	Wattage (W)	Cap Base	Luminous Flux Lamp (25°, lm)	Average Lifetime (hrs)	Colour Rendering Index (Ra)	Colour Temperature (K)	Min Order Quantity	Carton Quantity
TL5C22W830	22	2GX13	1800	12000	85	3000	10	10
TL5C22W840	22	2GX13	1800	12000	85	4000	10	10
TL5C40W830	40	2GX13	3300	12000	85	3000	10	10
TL5C40W840	40	2GX13	3300	12000	85	4000	10	10
TL5C55W830	55	2GX13	4200	12000	85	3000	10	10
TL5C55W840	55	2GX13	4200	12000	85	4000	10	10
TL5C60W830	60	2GX13	5000	12000	85	3000	10	10
TL5C60W840	60	2GX13	5000	12000	85	4000	10	10