

MASTER TL5 High Efficiency ECO


This extremely efficient TL5 lamp (tube diameter 16mm) saves considerable energy in quality T5 fittings. The TL5 HE Eco lamp offers excellent lumen maintenance and colour rendering. Application areas vary from offices and industry to schools and retail environments.

Benefits:

- Up to 10% energy saving with compatible current controlled ballasts
- The same quality of light as compared with MASTER TL5 HE lamps
- All benefits of regular TL5 lamps

Warnings and Safety:

- Energy reduction is only achieved with current-controlled gear
- The lamps operate with power-controlled gear, but in that case give more light output instead of using less energy.



Product ID	A max.	B max.	C max.	D max.
14W → 13W	549.0	556.1	563.2	17
21W → 19W	849.0	856.1	863.2	17
28W → 25W	1149.0	1156.1	1163.2	17
35W → 32W	1449.0	1456.1	1463.2	17

Dimensions in mm

MASTER TL5 High Efficiency Eco

Shortcode	Wattage (W)	Cap Base	Luminous Flux Lamp (35°, lm)	Average Lifetime (hrs)	Colour Rendering Index (Ra)	Colour Temperature (K)	Min Order Quantity	Carton Quantity
TL513W830ECO	13	G5	1350	25000	85	3000	40	40
TL513W840ECO	13	G5	1350	25000	85	4000	40	40
TL513W865ECO	13	G5	1250	25000	85	6500	40	40
TL519W830ECO	19	G5	2100	25000	85	3000	40	40
TL519W840ECO	19	G5	2100	25000	85	4000	40	40
TL525W830ECO	25	G5	2900	25000	85	3000	40	40
TL525W840ECO	25	G5	2900	25000	85	4000	40	40
TL525W865ECO	25	G5	2700	25000	85	6500	40	40
TL532W830ECO	32	G5	3650	25000	85	3000	40	40
TL532W840ECO	32	G5	3650	25000	85	4000	40	40
TL532W865ECO	32	G5	3400	25000	85	6500	40	40