


MASTER TL5 High Output ECO

This extremely efficient TL5 lamp (tube diameter 16mm) saves considerable energy by simple lamp-for-lamp replacement. The TL5 HO Eco lamp offers excellent lumen maintenance and colour rendering. Application areas vary from offices and industry to schools and retail environments.

- Benefits:**
- Up to 10% energy saving with compatible current controlled ballasts
 - The same quality of light as compared with MASTER TL5 HO lamps
 - All benefits of regular TL5 lamps

- Warnings and Safety:**
- Energy reduction is only achieved with current-controlled gear
 - The lamps operate with power-controlled gear, but in that case give more light output instead of using less energy.



Product ID	A max.	B max.	C max.	D max.
20W - 24W	549.0	556.1	563.2	17
34W - 39W	849.0	856.1	863.2	17
45W - 49W	1449.0	1456.1	1463.2	17
50W - 54W	1149.0	1156.1	1163.2	17
73W - 80W	1449.0	1456.1	1463.2	17

Dimensions in mm

MASTER TL5 High Output Eco

Shortcode	Wattage (W)	Cap Base	Luminous Flux Lamp (35°, lm)	Average Lifetime (hrs)	Colour Rendering Index (Ra)	Colour Temperature (K)	Min Order Quantity	Carton Quantity
TL520W830ECO	20	G5	1950	30000	85	3000	40	40
TL520W840ECO	20	G5	1950	30000	85	4000	40	40
TL534W830ECO	34	G5	3500	30000	85	3000	40	40
TL534W840ECO	34	G5	3500	30000	85	4000	40	40
TL545W830ECO	45	G5	4800	30000	85	3000	40	40
TL545W840ECO	45	G5	4800	30000	85	4000	40	40
TL545W865ECO	45	G5	4550	30000	85	6500	40	40
TL550W830ECO	50	G5	5000	30000	85	3000	40	40
TL550W840ECO	50	G5	5000	30000	85	4000	40	40
TL550W865ECO	50	G5	4650	30000	85	6500	40	40
TL573W830ECO	73	G5	7000	30000	85	3000	40	40
TL573W840ECO	73	G5	7000	30000	85	4000	40	40
TL573W865ECO	73	G5	6650	30000	85	6500	40	40