


# MASTER TL-D 90 De Luxe / Graphica

When natural colour reproduction is important the De Luxe and Graphica range of TL-D lamps offer a simple retro fit solution delivering very good (De Luxe CRI >90) and excellent (Graphica CRI >95) colour reproduction.

De Luxe Applications include first aid and treatment rooms in hospitals, printing rooms, jewellery, dentists, hairdressing, museums and shops etc.

Graphica Applications include the graphical industry, printing industry, photo shops, hospitals, etc.



Product ID max.	A max.	B max.	C max.	D max.	E max.
18W	589.8	594.5	96.9	604	28
36W	1199.4	1204.7	1206.5	1213.6	28
58W	1500.0	1504.7	1507.1	1514.2	28

Dimensions in mm

## MASTER TL-D 90 De Luxe

Shortcode	Wattage (W)	Cap Base	Voltage	Luminous Flux Lamp (lm)	Average Lifetime (hrs)	Colour Rendering Index (Ra)	Colour Temperature (K)	Min Order Quantity	Carton Quantity
928043593081	TLD18W930	18	G13	1200	20000	91	3000	10	10
928043594081	TLD18W940	18	G13	1200	20000	91	4000	10	10
928043595081	TLD18W950	18	G13	1150	20000	92	5000	10	10
928044593081	TLD36W930	36	G13	2800	20000	91	3000	10	10
928044594081	TLD36W940	36	G13	2800	20000	91	4000	10	10
928044595081	TLD36W950	36	G13	2800	20000	92	5000	10	10
928044596581	TLD36W965	36	G13	2800	20000	93	6500	10	10
928045093081	TLD58W930	58	G13	4350	20000	91	3000	10	10
928045094081	TLD58W940	58	G13	4600	20000	91	4000	10	10
928045095081	TLD58W950	58	G13	4550	20000	92	5000	10	10

## MASTER TL-D Graphica

Shortcode	Wattage (W)	Cap Base	Luminous Flux Lamp (25°, lm)	Average Lifetime EL (hrs)	Colour Rendering Index (Ra)	Colour Temperature (K)	Min Order Quantity	Carton Quantity
TLD18W950GRAPH	18	G13	950	20000	97	5300	25	25
TLD18W965GRAPH	18	G13	930	20000	98	6500	25	25
TLD36W950GRAPH	36	G13	2340	20000	97	5300	25	25
TLD36W965GRAPH	36	G13	2100	20000	98	6500	25	25
TLD58W950GRAPH	58	G13	3670	20000	97	5300	25	25
TLD58W965GRAPH	58	G13	3350	20000	98	6500	25	25