


MASTER TL-D ALTO

The difference is green. The ALTO lamp, a green flagship product, features technology that employs a unique capsule injection dosing system that delivers significantly less mercury into each tube; now only two milligrams. The lamps Next Generation triphosphor technologies ensures high light output, high lumen maintenance, and good colour rendering.

Features a distinct green end cap for easy identification for relamping. So make the switch to green!



Product ID	A max.	B max.	C max.	D max.
18W	589.8	596.9	604.0	28
36W	1199.4	1206.5	1213.6	28
58W	1500.0	1507.0	1514.2	28

Dimensions in mm

MASTER TL-D ALTO

Shortcode	Wattage (W)	Cap Base	Luminous Flux Lamp (25°, lm)	Average Lifetime EL (hrs)	Colour Rendering Index (Ra)	Colour Temperature (K)	Min Order Quantity	Carton Quantity
TLD18W830ALTO	18	G13	1350	20000	83	3,000	25	25
TLD18W840ALTO	18	G13	1350	20000	82	4,000	25	25
TLD18W850ALTO	18	G13	1310	20000	80	5,000	25	25
TLD18W865ALTO	18	G13	1275	20000	80	6,500	25	25
TLD36W830ALTO	36	G13	3250	20000	83	3,000	25	25
TLD36W840ALTO	36	G13	3250	20000	82	4,000	25	25
TLD36W850ALTO	36	G13	3170	20000	80	5000	25	25
TLD36W865ALTO	36	G13	3070	20000	80	6500	25	25
TLD58W830ALTO	58	G13	5150	20000	83	3000	25	25
TLD58W840ALTO	58	G13	5200	20000	82	4000	25	25
TLD58W850ALTO	58	G13	4950	20000	80	5000	25	25
TLD58W865ALTO	58	G13	4800	20000	80	6500	25	25