



# MASTER TL-D Secura

Next Generation triphosphor tube with protective coating. Outer sleeve keeps glass and other lamp components together in case of accidental lamp breakage. Suited for use in areas with open food and beverage areas, production facilities, sports facilities, animal enclosures etc.

Features a distinct blue-ring to identify as protected tubes. MASTER TL-D Secura is HACCP Certified.



Product ID	A max.	B max.	C max.	D max.
36W	1199.4	1206.5	1213.6	28
58W	500.0	1507.0	1514.2	28

Dimensions in mm

## MASTER TL-D Secura

Shortcode	Wattage (W)	Cap Base	Voltage	Luminous Flux Lamp (lm)	Average Lifetime (hrs)	Colour Rendering Index (Ra)	Colour Temperature (K)	Min Order Quantity	Carton Quantity
TLD36W840SECURA	36	G13		3200	20000	85	4000	25	25
TLD58W840SECURA	58	G13		5000	20000	85	4000	25	25