


# MASTER TL-D Super 80

Next Generation triphosphor tubes with alternate wattages/lengths.



Product ID	A max.	B max.	C max.	D max.
16W	589.8	596.9	604.0	28
23W	970.0	977.1	984.2	28
30W	894.6	901.7	908.8	28
32W	1199.4	1206.5	1213.6	28
38W	1047.0	1054.1	1061.2	28
50W	1500	1507.1	1514.2	28
70W	1763.8	1770.9	1778.0	28

Dimensions in mm

## MASTER TL-D Super 80

Shortcode	Wattage (W)	Cap Base	Luminous Flux Lamp (25°, lm)	Average Lifetime EL (hrs)	Colour Rendering Index (Ra)	Colour Temperature (K)	Min Order Quantity	Carton Quantity
TLD16W840	16	G13	1200	20,000	82	4000	25	25
TLD23W840	23	G13	2050	20,000	82	4000	25	25
TLD30W830	30	G13	2400	20,000	85	3000	25	25
TLD30W840	30	G13	2400	20,000	85	4000	25	25
TLD30W865	30	G13	2300	20000	80	6500	25	25
TLD32W840	32	G13	3200	20000	85	4000	25	25
TLD38W840	38	G13	3350	20000	85	4000	25	25
TLD50W840	50	G13	5000	20000	85	4000	25	25
TLD70W840	70	G13	6200	20000	85	4000	25	25