


# MASTER TL-D Xtreme

Next Generation triphosphor tube with long service life and fewer early failures. Xtreme (extremely long life) are suited for applications where maintenance costs are high; such as areas with high ceilings or difficult to reach areas (department stores, supermarkets, warehouses, halls, airports etc). The Xtreme lamps are also suited to areas that require minimum disruption due to relamping; such as production facilities and transport tunnels. Philips recommends Xtreme lamps in applications where users are looking for longer periods between group replacement of lamps. Features a distinct X-cap to identify as a long-life lamp.



Product ID	A max.	B max.	C max.	D max.
18W	589.8	596.9	604	28
36W	1199.4	1206.5	1213.6	28
58W	1500.0	1507.1	1514.2	28

Dimensions in mm

## MASTER TL-D Xtreme

Shortcode	Wattage (W)	Cap Base	Luminous Flux Lamp (25°, lm)	Average Lifetime EL (hrs)	Colour Rendering Index (Ra)	Colour Temperature (K)	Min Order Quantity	Carton Quantity
TLD18W830XTRE	18	G13	1350		85	3000	25	25
TLD18W840XTRE	18	G13	1350		85	4000	25	25
TLD18W865XTRE	18	G13	1250		85	6500	25	25
TLD36W830XTRE	36	G13	3250		85	3000	25	25
TLD36W840XTRE	36	G13	3250		85	4000	25	25
TLD36W865XTRE	36	G13	3150		85	6500	25	25
TLD58W840XTRE	58	G13	5150		85	4000	25	25
TLD58W865XTRE	58	G13	5000		85	6500	25	25