


Masterline 111

Low voltage halogen reflector lamp with double-ended burner and high-purity aluminium reflector. It has a unique infra-red coated burner technology, and revolutionary compact precision burner for maximum performance of the infra-red reflecting coating. The ceramic filament shield reduces glare and improves beam shape. It has a flat profile, very tight beam pattern, and excellent glare control.

Increased lifetime (4,000 hours) ensures low maintenance costs.



Product ID	Overall Length C max.	Overall Length C1 max.	Diameter D max.
30, 45, 60W	65	49	111
Dimensions in mm			

Masterline 111

Shortcode	Beam Angle	Wattage (W)	Cap Base	Voltage	Bulb Shape	Luminous Intensity (cd)	Average Lifetime (hrs)	Colour Temperature (K)	Unit	Carton Quantity
MASALR123024	24°	30	G53	240V	AR111	4000	4000	2700	PCE	6
MASALR124524	24°	45	G53	240V	AR111	5300	4000	2700	PCE	6
MASALR124545	45°	45	G53	240V	AR111	1900	4000	2700	PCE	6
MASALR126024	24°	60	G53	240V	AR111	8500	4000	2700	PCE	6
MASALR126045	45°	60	G53	240V	AR111	2800	4000	2700	PCE	6