


Mercury - High Pressure Ovoid

High pressure mercury vapour lamps with a quartz discharge tube enclosed in an internally coated ovoid outer bulb. For indoor or outdoor applications. HPL-N lamps require control gear to operate and have a universal burning position.



Product ID	C max.	D max.
50W	130	56
80W	155	71
125W	173	76
250W	226	91
400W	290	122

Dimensions in mm

HPL-N

Shortcode	Description	Wattage (W)	Cap Base	Luminous Flux (lm)	Average Lifetime (hrs)	Colour Temp (K)	Min Order Qty	Carton Qty
HPLN50	HPL-N 50W E27 SG 1CT/24	50	E27	1770	16000	4200	1	24
HPLN80	HPL-N 80W E27 SG 1CT/24	80	E27	3600	16000	4200	1	24
HPLN125	HPL-N 125W E27 SG 1CT/24	125	E27	6200	16000	4200	1	24
HPLN250	HPL-N 250W E40 HG 1CT/12	250	E40	12700	16000	4100	1	12
HPLN400	HPL-N 400W E40 HG 1CT/6	400	E40	22000	16000	4200	1	6