


Metal Halide – ArenaVision/OptiVision Lamps

MHN-SA/MHN-LA lamps with their excellent natural white colour, high luminous efficacy and compact size are designed to meet the demanding requirements of professional sports lighting and flood lighting applications. Double pinch concept results in longer lifetime. Available in short arc (MHN-SA) and long arc (MHN-LA) versions.

MHN-SA X830R



MHN-SA PSFC



Product ID	A max.	D max.	O max.	X nom.
1800W	364	41	25	N/A
2000W	364	41	25	25
2000W HO	226	34.3	25	34

Dimensions in mm


Metal Halide – Short Arc

Shortcode	Description	Wattage (W)	Cap Base	Voltage	Colour Rendering Index (Ra)	Luminous Flux (lm)	Average Lifetime (hrs)	Colour Temp (K)	Min Order Qty	Carton Qty	Trade Price
MHNSA1800W400V	MHN-SA 1800W /956 (P)SFC 400V UNP	1800	(P)SFC	400	86	160000	6100	5600	1	1	\$1,040.00
MHNSA2000W400V	MHN-SA 2000W /956 X830R 400V UNP	2000	X830R	400	90	200000	3700	5600	1	1	\$981.76
MHNSA2KW400VHO	MASTER MHN-SA 2000W/956 400V XW HO UNP/1	2000	X830R	400	81	226000	5000	5600	1	1	\$1,080.00

MHN-LA 2000W



MHN-LA 1000W



Product ID	C max.	D max.	L max.	O nom.
1800W/X830R	318	41	25	25
2000W/X830R	318	41	25	25
1800W (P) SFC	364	41	25	25

Dimensions in mm

Metal Halide – Long Arc

Shortcode	Description	Wattage (W)	Cap Base	Voltage	Colour Rendering Index (Ra)	Luminous Flux (lm)	Average Lifetime (hrs)	Colour Temp (K)	Min Order Qty	Carton Qty	Trade Price
MHNL1000W230V	MASTER MHN-LA 1000W/842 230V XWH	1000	X528	230	70	100000	15000	4200	1	1	\$860.00
MHNL1000W956	MASTER MHN-LA 1000W/956 230V XWH	1000	X528	230	80	90000	15000	5600	1	1	\$860.00
MHNL2000W400V	MASTER MHN-LA 2000W/842 400V XWH	2000	X528	400	72	220000	13000	4200	1	1	\$890.00
MHNL2000W956	MASTER MHN-LA 2000W/956 400V XWH	2000	X528	400	82	190000	13000	5600	1	1	\$890.00