


Metal Halide – Universal Operating Ovoid

Metal halide gas discharge lamps offer good luminous efficacy, good colour rendering and reliable long life. In anovoid style, with coated outer-bulb, and operates at any position.

Low wattage lamps with extra quartz tube around discharge tube prevents risk of outer bulb shattering when abnormally operated or at end of life.



Product ID	C max.	D max.	L max.
70W/100W/150W	141	56	83

Dimensions in mm

Metal Halide – Universal Operating Ovoid

Shortcode	Description	Type	Wattage (W)	Cap Base	Luminous Flux (lm)	Average Lifetime (hrs)	Colour Temp (K)	Min Order Qty	Carton Qty
MH70CO	MH 70W/640 P E27 CO SLV/24	Coated	70	E27	5300	10000	4000	24	24
MH70	MH 70W/640 P E27 CL SLV/24	Clear	70	E27	5600	10000	4000	1	24
MH100	MH 100W/640 P E27 CL SLV/24	Clear	100	E27	9000	10000	4000	1	24
MH150CO	MH 150W/640 P E27 CO SLV/24	Coated	150	E27	13000	10000	4000	24	24