


# PL-C 2-PIN

PL-C lamps are compact, single ended fluorescent lamps. All require external control gear which normally comes complete with the luminaire. 2-pin (non-dimming) option.



Product ID	Base Face to Base Face A max.	Insertion Length B max.	Overall Length C max.	Diameter D max.
10W	75.7	94	116.4	27.1
13W	97.7	116	138.4	27.1
18W	109.7	128	150.4	27.1
26W	130.7	149	171.4	27.1

Dimensions in mm

## PL-C 2-PIN

Shortcode	Wattage (W)	Cap Base	Luminous Flux Lamp (lm)	Average Lifetime (hrs)	Colour Temperature (K)	Min Order Quantity	Carton Quantity
PLC10W8272P	10	G24d-1	600	10000	2700	50	50
PLC10W8402P	10	G24d-1	600	10000	4000	1	50
PLC13W8272P	13	G24d-1	900	10000	2700	1	50
PLC13W8302P	13	G24d-1	900	10000	3000	1	50
PLC13W8402P	13	G24d-1	900	10000	4000	1	50
PLC18W8302P	18	G24d-2	1200	10000	3000	1	50
PLC18W8402P	18	G24d-2	1200	10000	4000	1	50
PLC26W8272P	26	G24d-3	1800	10000	2700	1	50
PLC26W8302P	26	G24d-3	1800	10000	3000	1	50
PLC26W8402P	26	G24d-3	1800	10000	4000	1	50
PLC26W8652P	26	G24d-3	1740	10000	6500	50	50