


PL-C 4-PIN

PL-C lamps are compact, single ended fluorescent lamps. All require external control gear which normally comes complete with the luminaire. 4-pin (dimming) option.



Product ID	A max.	B max.	C max.	D1 max.
13W	97.5	117	131.9	27.1
18W	109.5	129	143.9	27.1
26W	130.7	150	164.9	27.1

Dimensions in mm

PL-C 4-PIN

Shortcode	Wattage (W)	Cap Base	Luminous Flux Lamp (lm)	Average Lifetime (hrs)	Colour Rendering Index (Ra)	Colour Temp (K)	Min Order Quantity	Carton Qty
PLC13W8404P	13	G24q-1	900	13000	82	4000	1	50
PLC18W8304P	18	G24q-2	1200	13000	83	3000	1	50
PLC18W8404P	18	G24q-2	1200	13000	82	4000	1	50
PLC26W8304P	26	G24q-3	1760	13000	83	3000	1	50
PLC26W8404P	26	G24q-3	1760	13000	82	4000	1	50